

KIP-600P

Sonda pro kontrolu optických vláken




Specifikace

- 400 násobné zvětšení
jasně viditelné rozhraní optického vlákna
- Rozlišení < 1 μ m
- USB port kompatibilní s PC a NB (Windows).
OTDR(Komshine)
- Využití: UPC: SC/ FC/ ST/ LC/
SC Female/LC Female(v balení)
Applicable for APC: SC/SC (volitelně)
- Rychlé manuální ostření
- Lehké, přenosné, jednoduché na ovládání


Vlastnosti



400×
zvětšení



Dostupných
8 konektorů



USB
-Port



Jednokrokový
proces



Přesnost
roznášení
1 μ m

Univerzální kompatibilita



Platí pro UPC: SC/ FC/ ST/ LC/ SC Female/
LC Female (v balení)

Platí pro APC: SC/SC Female (Volitelně)



SC



FC



ST



LC




SC Female



LC Female

Jak použít



Produkt

Typ	KIP-600P sonda
Zvětšení	400X
Ostření	Manuální
Konektory	UPC: SC/ FC/ ST/ LC/ SC Female/LC Female (V balení) APC: SC/SC Female (Volitelně)
Video formát	NTSC/PAL
Skladovací teplota	-20°C~50°C
USB port	PC a NB (Windows), OTDR (Komshine)

Produktové foto



CONTACT US:

KomShine Technologies Limited

HEAD OFFICE:

2F Bldg. D Qinhen Tech. Pk. Nanjing, JS, 210001, China

TEL: +86 25 66047688

www.komshine.com

ventas@komshine.com

- * Komshine reserves the right to improve, enhance, or modify the features and specifications of KomShine products without prior notification.
- * Company and product names appearing in this catalogue are registered marks or trademarks of respective companies.
- * This catalogue is printed using environmentally friendly paper and ink.